

FMWCP1013 DATA SHEET

30 dB WR-62 Directional Waveguide Broadwall Coupler With UG-419/U Square Cover Flange and E-Plane Coupled Port from 12.4 GHz to 18 GHz

The FMWCP1013 is a WR-62 Directional Broadwall waveguide coupler that operates in the frequency range of 12.4 to 18 GHz. This Waveguide component has a typical VSWR of 1.05:1. These designs are made of painted copper alloy and incorporate a broad wall configuration that result in a mid-band nominal coupling value of 10, 20, or 30 dB. Common applications for this component would be where power measurements are required within a system for measuring/sampling power or frequency monitoring with minimal signal loss to the main transmission line. Fairview Microwave offers a complete family of waveguide Crossguide and Broadwall couplers that are in-stock and ship same day.

Electrical Specifications*

Description	Min	Тур	Мах	Units		
Frequency Range	12.4		18	GHz		
Directivity		40		dB		
Insertion Loss		0.15		dB		
Main Line VSWR		1.05:1				
Nominal Coupling Level		30		dB		
* Values at 25°C, sea						
chanical Specificat	ions					
Size Length Height Weight		2.836	13.75 in [349.25 mm] 2.836 in [72.03 mm] 0.915 lbs [415.04 g]			
Configuration Design Size			Directional E-Plane Broadwall WR-62			
Input Flange Flange Type Flange Designation Material Plating		UG-41	Square Cover UG-419/U Copper Alloy Silver			
Output Flange Flange Type Flange Designation Material Plating		UG-41	e Cover 19/U er Alloy			
Coupled Flange(s) Flange Type Flange Designation Material		UG-41	e Cover 19/U er Alloy			



Features:

- Broadwall Waveguide Coupler
- 30 dB Nominal Coupling Level
- 12.4 GHz to 18 GHz
 Frequency Range
- Body and Flanges made of Copper Alloy
- Low VSWR

Applications:

- Test Benches
- Radar
- Satellite
- Microwave Radio
- Attenuation Measurements
- Power Measurements
- Source Leveling

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com

Yes 12/17/2015

> REV 1.0 Page 1 of 5 Copyright © 2016







Plotted and Other Data

Notes:

• Values at 25 °C, sea level

Typical Performance Data






1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689








1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689



FMWCP1013 DATA SHEET



30 dB WR-62 Directional Waveguide Broadwall Coupler With UG-419/U Square Cover Flange and E-Plane Coupled Port from 12.4 GHz to 18 GHz from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: 30 dB WR-62 Directional Waveguide Broadwall Coupler With UG-419/U Square Cover Flange and E-Plane Coupled Port from 12.4 GHz to 18 GHz FMWCP1013

URL: https://www.fairviewmicrowave.com/30-db-wr-62-directional-waveguide-broadwall-coupler-ug419-square-e-fmwcp1013-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.







* THESE DIMENSIONS AND TOLERANCES SUPERSEDE NOTE #1 ON TITLE BLOCK.

FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].							
30 dB WR-62 Directional Waveguide Broadwall Coupler With UG-419/U Square Cover Flange and E-Plane Coupled Port from 12.4 GHz to 18 GHz	DWG NO FMWCP1013			CAGE CODE 3FKR5				
	CAD FILE 051016	SHEET	SCALE	E N/A	SIZE A	2233		

1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689