

SMA Male (Plug) Connector for RG316DS, RG188-DS Cable, Crimp/Solder



SC7067

Configuration

- SMA Male Connector
- MIL-STD-348A
- 50 Ohms
- Straight Body Geometry
- Connector Interface Types: RG316DS, RG188-DS
- 5/16 inch Hex

Features

- Operating Frequency of 12.4 GHz Max.
- Excellent VSWR of 1.21:1
- Gold Plated Brass Contact
- 30 μ m minimum contact plating

Applications

- General Purpose Test
- Custom Cable Assemblies

Description

SMA Male Standard Connector Crimp/Solder Attachment for RG316DS and RG188-DS Cable, part number SC7067, from Fairview Microwave is in-stock and ships same day. This SMA male connector operates up to a maximum frequency of 12.4 GHz and offers excellent VSWR of 1.21:1.

Fairview's SMA male connector SC7067 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		12.4	GHz
VSWR			1.21:1	
Operating Voltage (AC)			335	Vrms
Impedance		50		Ohms

Mechanical Specifications

Size

Length	0.85 in [21.59 mm]
Width	0.312 in [7.92 mm]
Height	0.312 in [7.92 mm]
Weight	0.011 lbs [4.99 g]
Mating Torque	7 to 10 in-lbs [0.79 to 1.13 Nm]

SMA Male (Plug) Connector for RG316DS,
RG188-DS Cable, Crimp/Solder



SC7067

Material Specifications

Description	Material	Plating
Contact	Brass	Gold 30 µin minimum
Insulation	PTFE	
Body	Passivated Stainless Steel	
Coupling Nut	Passivated Stainless Steel	

Mechanical Specification Notes:

Crimp Size Required: Contact: 0.92 (0.36) SQ. Crimp Tool. Ferrule: 3.9 (0.154) Hex. Crimp Tool.

Environmental Specifications

Temperature

Operating Range -65 to +165 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

SMA Male (Plug) Connector for RG316DS, RG188-DS Cable, Crimp/Solder from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: [SMA Male \(Plug\) Connector for RG316DS, RG188-DS Cable, Crimp/Solder SC7067](#)

URL: <https://www.fairviewmicrowave.com/sma-male-rg316ds-rg188-ds-connector-sc7067-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

SC7067 CAD Drawing

SMA Male (Plug) Connector for RG316DS, RG188-DS Cable, Crimp/Solder



Fairview Microwave®
an INFINIT® brand

Website: www.FairviewMicrowave.com
Phone: 1.800.715.4396 | 1.972.649.6678

INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5

SCALE: NONE
SHEET: 1 OF 1

DESCRIPTION: SMA MALE (PLUG) CONNECTOR FOR RG316DS, RG188-DS CABLE, CRIMP/SOLDER

REV	DESCRIPTION	DATE	BY	CHKD
B	SC7067			

SIZE	CAGE CODE	DRAWN BY	ITEM NO.
A	3FKR5	DFRISIELLO	SC7067