

N T Adapter Female Male Female

Electrical Specifications

Frequency Range DC to 4 GHz

Mechanical Specifications

Size

Length 1.75 in [44.45 mm]

Height 1.47 in [37.34 mm]

Weight 0.17549 lbs [79.6 g]

Connector 1

Type

Mating Cycles

Inner Conductor Material and Plating

Body Material and Plating

Dielectric Type

N Female

500

Beryllium Copper, Silver

Nickel, Silver

PTFE

Connector 2

Type

Mating Cycles

Inner Conductor Material and Plating

Body Material and Plating

Dielectric Type

N Male

500

Beryllium Copper, Silver

Nickel, Silver

PTFE

Connector 3

Type

Mating Cycles

Inner Conductor Material and Plating

Body Material and Plating

Dielectric Type

N Female

500

Beryllium Copper, Silver

Nickel, Silver

PTFE

Environmental Specifications

Temperature

Operating Range -65 to +165 deg C

Compliance Certifications (visit www.FairviewMicrowave.com for current document)

RoHS Compliant Yes

Plotted and Other Data

Notes:

- Values at 25 °C, sea level



Features:

- Connector 1: N Female
- Impedance 1: 50 Ohms
- Connector 2: N Male
- Impedance 2: 50 Ohms
- Connector 3: N Female
- Adapter Design: Standard
- Body Style: Tee


Fairview Microwave
1130 Junction Dr. #100
Allen, TX 75013
Tel: 1-800-715-4396 / (972) 649-6678
Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com


N T Adapter Female Male Female from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [N T Adapter Female Male Female SM4577](#)

URL: <http://www.fairviewmicrowave.com/n-female-male-female-tee-adapter-sm4577-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.





FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

NOTES:

1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].

TITLE

N T Adapter Female Male Female

DWG NO

SM4577

CAGE CODE

3FKR5

CAD FILE

011415

SHEET

SCALE N/A

SIZE A

5568