

TNC Female to ZMA Plug Push-On 4 Hole Flange Adapter

Configuration

Connector 1	TNC Female
Connector 2	Push-On ZMA Plug
Impedance	50 Ohms
Body Style	Straight



Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		12.4	GHz
VSWR			1.35:1	
Dielectric Withstanding Voltage (AC)			2,500	Vrms

Mechanical Specifications

Size	
Length	0.91 in [23.11 mm]
Width	0.687 in [17.45 mm]
Weight	0.02513 lbs [11.4 g]

Description	Connector 1	Connector 2
Type	TNC Female	ZMA Plug
Polarity	Standard	Standard
Mating Cycles	500	

Material Specifications

Description	Connector 1	Connector 2
Type	TNC Female	ZMA Plug
Contact Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Contact Plating Specification	MIL-G-45204	MIL-G-45204
Insulation Material	PTFE	PTFE
Body Material and Plating	Passivated Stainless Steel	Passivated Stainless Steel

Compliance Certifications (visit www.FairviewMicrowave.com for current document)


RoHS Compliant

Plotted and Other Data

Notes:

Fairview Microwave
1130 Junction Dr. #100
Allen, TX 75013
Tel: 1-800-715-4396 / (972) 649-6678
Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Typical Performance Data




TNC Female to ZMA Plug Push-On 4 Hole Flange Adapter from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [TNC Female to ZMA Plug Push-On 4 Hole Flange Adapter SM5762](http://www.fairviewmicrowave.com/tnc-female-zma-plug-push-on-4-hole-flange-adapter-sm5762-p.aspx)

URL: <http://www.fairviewmicrowave.com/tnc-female-zma-plug-push-on-4-hole-flange-adapter-sm5762-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE
TNC Female to ZMA Plug Push-On 4 Hole Flange
Adapter

NOTES:

1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].

DWG NO

SM5762

CAGE CODE

3FKR5

CAD FILE

011415

SHEET

SCALE N/A

SIZE A

5568