

TNC/MALE-TNC/FEMALE REVERSE POLARITY 3 GHZ ATTENUATORS

SA3TR-XX

SPECIFICATIONS

ELECTRICAL


FREQUENCY: 0-3 GHZ
 IMPEDANCE: 50 OHMS
 VSWR: 1.25:1 MAX
 POWER: 2 WATT CW @ 25 DEG C
 POWER(PEAK): 100W FOR 25μSECONDS
 POWER COEFFICIENT: 0.001dB/W

ATTENUATION ACCURACY		
	DC-2 GHz	2-3 GHz
10 dB	± 0.2 dB	± 0.3 dB

MECHANICAL

MATERIALS BODY : BRASS
 BODY PLATING: TRI-METAL (TIN-ZINC-COPPER-ALLOY)
 MATERIALS CONTACT: PHOSPHER BRONZE

ROHS COMPLIANCE



				FAIRVIEW MICROWAVE INC.			
				ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM			
				TITLE			
				TNC/MALE-TNC/FEMALE REVERSE POLARITY 3 GHZ ATTENUATORS			
SIZE		CAGE CODE		DWG NO		REV	
A		3FKR5		SA3TR-XX		--	
SCALE				SHEET			