

FM15B5007 DATA SHEET

225 MHz to 512 MHz, SMA, Bi-Directional Amplifier, VHF/UHF, 16W Psat, 36dB Tx Gain, 35% Efficiency, 8 microsec speed, Manual T/R Control

The FM15B5007 is a Class AB high power Bi-Directional Amplifier that operates in VHF/UHF bands from 225 MHz to 512 MHz. This amplifier generates 16 watts typical Psat (4W linear) RF output power to boost performance of datalinks and transmitters. The design is highly efficient with 35% efficiency and the small form factor package is ideal for size, weight, and power (SWaP) constrained applications used in broadband RF telemetry, tactical communication, electronic warfare, and unmanned aircraft and ground systems, as well as software defined radios. Impressive typical performance includes 36 dB of transmit gain, 15 dB of receive gain, 8 µsec switching speed, and harmonic suppression of -13 dBc. Operating voltage is +28 Vdc with 1.6A of DC current. Additional features include manual T/R control, single power supply, and overvoltage protection. For TTL logic on/off control, transmit mode uses 0V or ground and receive mode uses N/C or +5V. The rugged Mil-Grade assembly supports female SMA RF input/ output connectors and a micro-D 9 pin socket command control connector with an accessory cable assembly included. The operating baseplate temperature range is -40°C to +85°C and the unit is guaranteed to withstand up to 95% relative humidity, altitude levels up to 30,000 ft, and random vibration and shock profiles (see chart below). Pasternak also offers an accessory Harmonic filter option, model FMHFL0001 that can be used at the output of the FM15B5007 power amplifier. This lowpass RF filter covers 2.5 GHz to 6 GHz and has low insertion loss with power handling up to 50W and specifically designed to reduce harmonics at the output of transmitters operating at up through C-Band and offers rejection levels of greater than 20 dB from 8 GHz to 10 GHz. The filter is offered in a miniature SMA connectorized package.

Electrical Specifications (TA = +25°C, DC Voltage = 28Volts DC Current = 1.6A)

Transmit

Description	Min	Тур	Max	Unit
Frequency Range	225		512	MHz
Output Power (Linear)*		4		Watts
Psat Output Power		16		Watts
RF Input Power		+5	+10	dBm
Gain		36		dB
Gain Flatness			±0.75	dB
Gain Flatness Over Temperatur	re	1		dB
2nd Harmonics			-13	dBc
Spurious			-50	dBc
Operating DC Voltage	10	28	32	Volts
Current Draw		1.6	2.5	Α
Quiescent Current (biased)		340		mA
Switching Time		8	10	uSec
Efficiency		35		%
Output Mismatch VSWR			10:1	
Input VSWR		2:1		

*-33 dBc ACLR, PIN = 5 dBm

Receive

Description	Min	Тур	Max	Unit



Features:

- Bi-Directional GaN High Power Amplifier
- 16W Psat (4W Liner)
 Output Power
- VHF/UHF Band Class AB Design
- Frequency Range: 225
 MHz to 512 MHz
- 36 dB Transmit Gain
- 15 dB Receive Gain
- Manual T/R Control
- Switching Speed 8 usecPAE: 35%
- +5V TTL Logic Control
- Small Form Factor Rugged Mil-Grade Package
- 50 Ohm Design
- Female SMA RF Connectors
- +28Vdc @ 1.6A DC Current
- -40°C to +85°C Operating Baseplate Temperature
- Output Harmonic Filter Accessory Option

Applications:

- Unmanned Aircraft (UAS) Group 2 &3
- Unmanned Ground Vehicles (UGV)
- RF Telemetry
- RF Communications Systems
- Software Defined Radios
- Data Links
- Transmitters
- Test & Measurement
- Telecom Infrastructure

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056

Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





1 dB Compression Point	+3		dBm
Gain	15		dB
Gain Flatness		±0.5	dB
Noise Figure	2.5		dB
Current Draw	175	200	mA

Protections

Parameter	Rating	Unit
Max Device Voltage	32	V
Max Device Current @ 10 VDC	7	А
Max Device Current @ 28 VDC	2.75	А
Max Device Current @ 32 VDC	2.5	А
Max RF Input Power @ ANT Port, $Z_L = 50 \Omega$	+30	dBm
Max RF Input Power @ XCVR Port, $Z_L = 50 \Omega$	+20	dBm
Max Operating Temperature (baseplate)	85	°C
Max Storage Temperature	100	°C



ESD Sensitive Material, Transport material in Approved ESD bags. Handle only in approved ESD Workstation.

Mechanical Specifications

Size

Length 2.34 in [59.44 mm]
Width 2.34 in [59.44 mm]
Height 0.7 in [17.78 mm]
Weight 0.2 lbs [90.72 g]
RF Connector (Input) SMA Female
RF Connector (Output) SMA Female

RF Connector (Output)


SMA Female

DC Connector

Micro-D, 9-Pin Socket

Environmental Specifications

Vibration / Shock Profile (Random profile in x,y, z axis, as per Figure for 15 minute duration in each axis)



Temperature

Operating Range -40 to +85 deg C Storage Range -55 to +85 deg C

Humidity 95%


301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689





Altitude

MIL-STD-810F Method 5004







Compliance Certifications (see product page for current document) Plotted and Other Data

Notes:

Values at +25 °C, sea level

Amplifier Power-up Precautions

- 1.) Confirm that proper ESD precautions and controls are always in place before handling any Amplifier module.
- 2.) Confirm adequate thermal management is in place to effectively dissipate heat away from the Amplifier package. The Amplifier operational baseplate temperature must be within the operational temperature range stated in the Amplifier datasheet. Depending on the design and thermal requirements, using a heatsink with cooling fan is always recommended for safe reliable operation. A heat sink without a cooling fan may also be used. Damage caused from overheating will void the warranty.
- 3.) Confirm adequate system grounding is established. The DC power supply and Amplifier must have a common ground in order to operate properly.
- 4.) Power Amplifiers may require additional DC Current when initially powered-up. Depending on the design, the input current draw could range from an additional 10% to 100% above the maximum rated DC current of the Amplifier. This varies based on product part number.
- 5.) Confirm the DC power supply, if limited, is set to allow for additional start-up current that's rated for the Power Amplifier.
- 6.) Confirm the system is designed and calibrated for 50 ohms. Any impedance mismatch may cause performance issues.
- 7.) Perform a CALIBRATION (if required) with the loads before connecting the Amplifier to the Network Analyzer to ensure proper performance.
- 8.) Use a fixed attenuator between the signal source and input port of the Amplifier to optimize the input VSWR match.
- 9.) Confirm the input power level at the input port of the amplifier does not exceed the maximum rated limit for input power (as stated in the Amplifier datasheet).

Pin for Small Signal Gain = P1dB-SSG-10 dB


Pin for P1dB = P1dB-SSG+1 dB

- 10.) Confirm the Network Analyzer is always connected to the Amplifier first before DC power is applied to the Amplifier.
- 11.) As long as the input and output ports of the amplifier are connected to a 500hm load and RF signal power is applied, the Amplifier can be powered up with DC voltage.
- 12.) Confirm the Amplifier output load is matched for a 50 Ohm impedance and will not exceed the maximum rated VSWR or Return Loss limit for the Amplifier. Exceeding the maximum rated VSWR or Return Loss limit will result in reflected signal power that could damage the Amplifier and void the warranty.
- 13.) Power Amplifier connected to an Antenna for signal transmission It's strongly recommended to use a high power fixed attenuator pad or an Isolator between the output port of the Amplifier and input port to the antenna. Any reflected signal power due to impedance mismatch will likely damage the Amplifier and void the warranty.
- 14.) The attenuator or isolator used at the output port of the Amplifier must be rated to handle the output power level and operational frequency band of the amplifier.


301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689








Typical Performance Data






301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689











225 MHz to 512 MHz, SMA, Bi-Directional Amplifier, VHF/UHF, 16W Psat, 36dB Tx Gain, 35% Efficiency, 8 microsec speed, Manual T/R Control from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: 225 MHz to 512 MHz, SMA, Bi-Directional Amplifier, VHF/UHF, 16W Psat, 36dB Tx Gain, 35% Efficiency, 8 microsec speed, Manual T/R Control FM15B5007

URL: https://www.fairviewmicrowave.com/high-power-bi-directional-amplifier-16-watts-512-mhz-sma-fm15b5007-p.aspx







