an INFINIT® brand

FMCA1713 DATA SHEET

Low Loss N Male to SMA Male Cable LL160 Coax

The N Male to SMA Male low loss cable using LL160 coax, part number FMCA1713, from Fairview Microwave is in-stock and ships same day. This N to SMA low loss cable assembly features a 82.5% velocity dielectric manufactured from expanded PTFE tape. This microporous dielectric contributes to the low loss and phase stability of the cables. Our triple shielded coaxial cable construction of Fairview's low loss LL160 provides shielding levels as high as 95 dB. The precision connections are constructed with stainless steel bodies and high temperature insulators, supporting a wide range of temperature from -55 to +165 degrees C. This solid combination of connectors and low loss coax are further enhanced with the addition of heavy-duty heat shrink for improved strain relief for this superior quality RF cable assembly.

Fairview's N Male to SMA Male low loss cable FMCA1713 datasheet, specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and high speed digital connections allows designers to configure and customize their signals however they like. From reducing losses or improving phase stability, Fairview microwave has the right low loss cable solutions to meet your needs.

Electrical Specifications

· · · · · · · · · · · · · · · · · · ·						
Description	Min	Т	ур	Max	ι	Inits
Frequency Range	DC			18		GHz
VSWR				1.35:1		
Velocity of Propagation		82	2.5			%
RF Shielding	-90					dB
Capacitance		25 [8	32.02]		pF/f	t [pF/m]

Performance by Frequency

-	-	-				
Description	F1	F2	F3	F4	F5	Units
Frequency	1	2	4.5	9	18	GHz
Insertion Loss (Typ.)	0.1	0.14	0.22	0.32	0.46	dB/ft
	0.33	0.46	0.72	1.05	1.51	dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.04*SQRT(F(GHz))dB maximum per connector.

Mechanical Specifications

Cable Assembly

Length* Weight

Cable

Cable Type Impedance Inner Conductor Type Inner Conductor Material and Plating Dielectric Type Number of Shields Shield Layer 1 0 in [0 mm] 0.12 lbs [54.43 g]

LL160 50 Ohms Solid Copper, Silver PTFE 3 Silver Plated Copper



Configuration:

- N Male
- SMA Male
- LL160

Features:

- Max Frequency 18 GHz
- Shielding Effectivity > -90 dB
- 82.5% Phase Velocity
- Triple Shielded
- FEP Jacket
- Low VSWR of 1.35:1 to 18 GHz
- -55 to +150 Temperature Range
- Expanded PTFE Tape Dielectric
- Same Day Shipment of Custom Lengths

Applications:

- General Purpose
- Laboratory Use
- Automated Test Systems
- Military Electronics
- Phased Array Antennas
- RF Countermeasures

Cable Diagram:





Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com Fairview Microwave

an INFINIT^C brand

FM	CA171 3	B
DATA	SHEET	

Shield Layer 2 Shield Layer 3	Aluminum Polyester Silver Plated Copper
Jacket Material	FEP
Jacket Diameter	0.16 in [4.06 mm]

Repeated Minimum Bend Radius

0.8 in [20.32 mm]

Connectors

Description	Connector 1	Connector 2		
Туре	N Male	SMA Male		
Impedance	50 Ohms	50 Ohms		
Contact Material & Plating	Beryllium Copper, Gold	Beryllium Copper, Gold		
Contact Plating Spec.	ASTM-B488	ASTM-B488		
Dielectric Type	PTFE	PTFE		
Body Material & Plating	Passivated Stainless Stee	Passivated Stainless Steel		
Coupling Nut Material & Pla	ating Passivated Stainless Stee	Passivated Stainless Steel		

Environmental Specifications

Temperature Operating Range

-55 to +165 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

How to Order

Part Numbe	er Configura	tion:	FMCA1713	- xx	uu	
						cm = Centimeters <blank> = Inches Length</blank>
Example:		12 = 12 inches lon 100cm = 100 cm lo				

Low Loss N Male to SMA Male Cable LL160 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: Low Loss N Male to SMA Male Cable LL160 Coax FMCA1713


URL: https://www.fairviewmicrowave.com/low-loss-n-male-sma-male-cable-ll160-coax-fmca1713-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689