



# SMA Male to BNC Male Right Angle Cable Using RG223 Coax

The SMA male to RA BNC male cable using RG223 coax, part number FMCA2689, from Fairview Microwave is in-stock and ships same day. This Fairview SMA to BNC cable assembly has a male to male gender configuration with 50 ohm flexible RG223 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMCA2689 SMA male to BNC male cable assembly operates to 4 GHz. The right angle BNC interface on the RG223 cable allows for easier connections in tight spaces. The double shielding of this Fairview cable assembly provides excellent shielding effectiveness.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

# **Electrical Specifications**

Description	Min	T,	ур	Max	U	Inits
Frequency Range	DC			4		GHz
Velocity of Propagation		6	6			%
Capacitance		30.8 [	101.0	5]	pF/fl	[pF/m]

# **Performance by Frequency**

Description	F1	F2	F3	F4	F5	Units
Frequency	0.1	0.25	0.5	1	4	GHz
Insertion Loss (Typ.)	0.04	0.061	0.09	0.134	0.291	dB/ft
	0.13	0.2	0.3	0.44	0.95	dB/m

## **Electrical Specification Notes:**

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1 dB for the straight connector and 0.2 dB for the right angle connector.

## **Mechanical Specifications**

## **Cable Assembly**

Weight 0.107 lbs [48.53 g]

## Cable

Cable Type
Impedance
Inner Conductor Type
Inner Conductor Material and Plating
Dielectric Type
Number of Shields
Shield Layer 1
Shield Layer 2
Jacket Material

RG223 50 Ohms Solid Copper, Silver PE

<u>2</u> Silver Plate

Silver Plated Copper Braid Silver Plated Copper Braid PVC, Black



# **Configuration:**

- SMA Male
- BNC Male Right Angle
- RG223

## **Features:**

- Max Frequency 4 GHz
- 66% Phase Velocity
- Double Shielded
- PVC Jacket

# **Applications:**

- General Purpose
- Laboratory Use

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689

www.fairviewmicrowave.com sales@fairviewmicrowave.com





Jacket Diameter 0.21 in [5.33 mm]

One Time Minimum Bend Radius 1 in [25.4 mm]

#### **Connectors**

Description	Connector 1	Connector 2		
Туре	SMA Male	BNC Male		
Specification	MIL-STD-348A			
Impedance	50 Ohms	50 Ohms		
Contact Material & Plating	Brass, Gold			
Contact Plating Spec.	50μ in. minimum			
Dielectric Type	Teflon			
Body Material & Plating	Brass, Nickel	Brass, Nickel		
Body Plating Spec.	100μ in. minimum	100μ in. minimum		
Hex Size	5/16 in			
Torque	5 in-lbs 0.57 Nm			


**Compliance Certifications** (see product page for current document)

## **Plotted and Other Data**

Notes:

• Values at 25°C, sea level.

## **How to Order**



SMA Male to BNC Male Right Angle Cable Using RG223 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: SMA Male to BNC Male Right Angle Cable Using RG223 Coax FMCA2689

URL: https://www.fairviewmicrowave.com/sma-male-to-ra-bnc-male-cable-rg223-coax-and-rohs-fmca2689-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689





