



# SMA Male Right Angle to BNC Female Bulkhead Cable Using RG223 Coax

The RA SMA male to BNC female bulkhead cable using RG223 coax, part number FMCA2714, from Fairview Microwave is in-stock and ships same day. This Fairview SMA to BNC cable assembly has a male to female gender configuration with 50 ohm flexible RG223 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMCA2714 SMA male to BNC female cable assembly operates to 4 GHz. The right angle SMA interface on the RG223 cable allows for easier connections in tight spaces. Our RF cable assembly with BNC bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications. The double shielding of this Fairview cable assembly provides excellent shielding effectiveness.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

### **Electrical Specifications**

Description	Min	T	ур	Max	U	Inits	
Frequency Range	DC			4		GHz	
VSWR				1.4:1			
Velocity of Propagation		$\epsilon$	6			%	
Capacitance	pacitance		30.8 [101.05]			pF/ft [pF/m]	
Operating Voltage (AC)				500	V	rms/	

### **Performance by Frequency**

Description	F1	F2	F3	F4	F5	Units
Frequency	0.1	0.25	0.5	1	4	GHz
Insertion Loss (Typ.)	0.04	0.061	0.09	0.134	0.291	dB/ft
	0.13	0.2	0.3	0.44	0.95	dB/m

### **Electrical Specification Notes:**

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1 dB for the straight connector and 0.2 dB for the right angle connector.

### **Mechanical Specifications**

### **Cable Assembly**

Weight 0.093 lbs [42.18 g]

#### Cable

Cable Type RG223
Impedance 50 Ohms
Inner Conductor Type Solid
Inner Conductor Material and Plating Copper, Silver
Dielectric Type PE



# **Configuration:**

- SMA Male Right Angle
- BNC Female Bulkhead
- RG223

### Features:

- Max Frequency 4 GHz
- 66% Phase Velocity
- Double Shielded
- PVC Jacket

## **Applications:**

- General Purpose
- · Laboratory Use

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com

sales@fairviewmicrowave.com





Number of Shields

Shield Layer 1 Silver Plated Copper Braid Silver Plated Copper Braid Silver Plated Copper Braid

2

Jacket Material PVC, Black

Jacket Diameter 0.209 in [5.31 mm]

Repeated Minimum Bend Radius 1 in [25.4 mm]

### **Connectors**

Description	Connector 1	Connector 2				
Туре	SMA Male	BNC Female				
Mount Method		Bulkhead				
Specification	MIL-STD-348A	MIL-STD-348A				
Impedance	50 Ohms	50 Ohms				
Contact Material & Plating	Brass, Gold	Brass, Gold				
Contact Plating Spec.	50 μin minimum	30 µin minimum				
Dielectric Type	PTFE	PTFE				
Body Material & Plating	Brass, Nickel	Brass, Nickel				
Body Plating Spec.	100 μin minimum	100 µin minimum				
Coupling Nut Material & Pla	ting Brass, Nickel					
Coupling Nut Plating Spec.	100 μin minimum	1				
Hex Size	5/16 inch					
Torque	3 in-lbs 0.34 Nm	1				

### **Environmental Specifications**

**Temperature** 

Operating Range -40 to +80 deg C

**Compliance Certifications** (see product page for current document)

### **Plotted and Other Data**

Notes:

• Values at 25°C, sea level.

### **How to Order**

Part Number Configuration:

Example: FMCA2714-12 = 12 inches long cable

FMCA2714-100cm = 100 cm long cable





SMA Male Right Angle to BNC Female Bulkhead Cable Using RG223 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: SMA Male Right Angle to BNC Female Bulkhead Cable Using RG223 Coax FMCA2714

URL: https://www.fairviewmicrowave.com/ra-sma-male-to-bnc-female-bulkhead-cable-rg223-coax-and-rohs-fmca2714-p. aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order

	ent improvements.				-			_				
	specifications are											
	of the part describ				purpose,	and Fair	view Mi	crowave	does no	ot assume	any I	iability
arising out	of the use of any	part or docu	menta	tion.								





