

SM4413 DATA SHEET

TNC Male to TNC Female Adapter IP67 Mated

Electrical Specifications

Frequency Range DC to 6 GHz Maximum VSWR 1.2:1

Mechanical Specifications

Size

Length 1.323 in [33.6 mm]

Connector 1

Type
Inner Conductor Material and Plating
Coupling Nut Material and Plating
Body Material and Plating
Dielectric Type

Connector 2

Type
Inner Conductor Material and Plating
Body Material and Plating
Dielectric Type

Environmental Specifications Temperature

Operating Range

Ingress Protection

TNC Male Brass, Gold Brass, Tri-Metal Brass, Tri-Metal PTFE

TNC Female Brass, Gold Brass, Tri-Metal PTFE

-40 to +120 deg C

IP67 Mated

H Commave

Features:


- Ingress Protection: IP67 Mated
- Connector 1: TNC Male
- Impedance 1: 50 Ohms
- Connector 2: TNC Female
- Impedance 2: 50 Ohms
- Adapter Design: Standard
- Body Style: Straight

Plotted and Other Data

Notes:

· Values at 25 °C, sea level

Power Data



Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013

Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com






TNC Male to TNC Female Adapter IP67 Mated from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: TNC Male to TNC Female Adapter IP67 Mated SM4413

URL: http://www.fairviewmicrowave.com/tnc-male-tnc-female-adapter-sm4413-p.aspx









FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
TNC Male to TNC Female Adapter IP67 Mated	DWG NO SM4413			CAGE CODE 3FKR5		
	CAD FILE 061014	SHEET	SCALE	E N/A	SIZE A	2233