

BNC M/F 3 GHZ ATTENUATORS

SA03B-XX

SPECIFICATIONS

ELECTRICAL

FREQUENCY: 0-3 GHZ
 IMPEDANCE: 50 OHMS
 VSWR: 1.2:1 @ 2 GHZ
 1.3:1 @ 3 GHZ
 POWER: 2 WATTS AVERAGE
 ATTENUATION ACCURACY: ± 0.5 dB


MECHANICAL

MATERIALS BODY : NICKEL PLATED BRASS
 MATERIALS CONTACT MALE: Au PLATED BRASS
 MATERIALS CONTACT FEMALE: Au PLATED BeCu
 INSULATOR: PTFE
 CONTACT PLATING: Au

ROHS COMPLIANT

BNC-M

BNC-F



				FAIRVIEW MICROWAVE INC.	
				ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	
				TITLE	
				BNC M/F 3 GHZ ATTENUATORS	
SIZE	CAGE CODE	DWG NO	REV		
A	3FKR5	SA03B-XX	--		
SCALE			SHEET		