

ATTENUATORS N M/F 18GHZ 100W

SA18N100W-XX

SPECIFICATIONS

ELECTRICAL:

FREQUENCY: 0-18 GHZ

VSWR 1.20 MAX TO 8 GHZ
 1.25 MAX TO 12 GHZ
 1.35 MAX TO 18 GHZ

POWER (AVG) 100 WATTS @ 25° C

POWER (PEAK) 1000 WATTS
 (5 μSEC PULSE WIDTH; 2.5% DUTY CYCLE)
 DERATED LINEARLY TO 10 WATTS @ 125° C

IMPEDANCE: 50 OHMS

ATTENUATION ACCURACY: 10DB +/- .75db;
 20db +/- 1.0db; 30, 40db +/- 1.2 db

BIDIRECTIONAL: 1-6 DB

UNIDIRECTIONAL: 10-40 DB

MECHANICAL:

MATERIAL CONNECTORS: PASSIVATED STAINLESS STEEL

MATERIAL RING & CONTACTS: BeCu


CENTER CONTACT: GOLD PLATED PER MIL-G-45204

INTERFACE: MIL-STD-348B

INSULATOR: TEFLON

TEMP: -55°C TO +125°C

ROHS COMPLIANT



MALE IS INPUT BY DEFAULT
 FEMALE INPUT P/N: SA18N100-XXFM

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

ATTENUATORS N M/F 18GHZ 100W

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SA18N100W-XX	A
SCALE		SHEET	