

ATTENUATORS N 25 WATTS 18GHZ

SA18N25-XX

SPECIFICATIONS


ELECTRICAL:

FREQUENCY: 0-18 GHZ
 VSWR @ 6 GHZ: 1.20 MAX
 VSWR @ 12.4 GHZ: 1.30 MAX
 VSWR @ 18 GHZ: 1.40 MAX
 POWER (AVG) 25 WATTS @ 25 DEG C
 POWER (PEAK) 500 WATTS
 ATTENUATION ACCURACY: GREATER OF
 +/-0.3DB OR 2.5% @ 6GHZ; +/- .5DB OR
 3% @ 12.4GHZ; .75DB OR 3.5% @ 18GHZ
 IMPEDANCE: 50 OHMS


TEMP: -65° TO +125° C
 CONNECTORS: PASS. STAINLESS STEEL
 CONTACTS: BeCU, Au PLATING MIL-G-45204
 HEAT SINK: BLACK ANNOXIDIZED ALUMINUM
 INTERFACE: MIL-STD-348B

ROHS COMPLIANT

2.30"



2.30"



2.46"

4.20"

				FAIRVIEW MICROWAVE INC.	
				ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	
				TITLE	
				ATTENUATORS N 25 WATTS 18GHZ	
SIZE	CAGE CODE	DWG NO		REV	
A	3FKR5	SA18N25-XX		--	
SCALE			SHEET		