

ATTENUATORS SMA M/F 26.5GHZ

SA26B-XX

SPECIFICATIONS

ELECTRICAL:

FREQUENCY: 0-26.5 GHZ

VSWR 1.50:1 MAX TO 26.5 GHZ

1.35:1 MAX TO 18GHZ

POWER (AVG) 2 WATTS @ 25 DEG C

POWER (PEAK) 500 WATTS

IMPEDANCE: 50 OHMS

ATTENUATION ACCURACY:

+/- 0.5 1-10 DB

+/- 1.0 11-20 DB

+/- 1.5 21-30 DB

MECHANICAL:

MATERIAL BODY: PASSIVATED STAINLESS STEEL

MATERIAL RING & CONTACTS: BeCu

CENTER CONTACT: GOLD PLATED PER MIL-G-45204


RESISTIVE ELEMENT: AINi SUBSTRATE T Ni RESISTOR

RECOMMENDED TORQUE: 7-9 IN-LBS

ENVIRONMENTAL:

TEMP: -55 C TO +125 C

ROHS COMPLIANT



FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

ATTENUATORS SMA M/F 26.5GHZ

SIZE

A

CAGE CODE

3FKR5

DWG NO

SA26B-XX

REV

A

SCALE

SHEET