

WR-28 Standard Waveguide Horn With UG-599/U Square Cover Flange and 15 dBi Nominal Gain Operating From 26.5 GHz to 40 GHz Frequency Range

Fairview Microwave's SH128-15 WR-28 waveguide standard gain horn antenna operating from 26.5 GHz to 40 GHz with a nominal 15 dBi gain is part of our full line of RF components available for same-day shipping. This pyramidal horn antenna has a lightweight anodized aluminum body and a precision tolerance UG-599/U square cover flange. The SH128-15 WR-28 waveguide standard gain horn antenna offers low gain variation across its operating frequency range and 32.1 degrees of half power beam width.

Waveguide standard gain horn antennas are used in a wide variety of applications due to their high power handling capability, low loss, high directivity, and near constant electrical performance across a broad bandwidth. Fairview Microwave's WR-28 standard gain horns are available in 10, 15 and 20 dB models with pyramidal shape and rectangular waveguide input.

Configuration

Design	WR-28 Standard Gain Horn
Pattern	Directional
Polarization	Linear

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	26.5		40	GHz
Nominal Gain		15		dBi
Horizontal 3dB Beam Width		31.3		Deg
Vertical 3dB Beam Width		32.1		Deg

Electrical Specification Notes:

3 dB beam width is calculated by computer simulation.

Mechanical Specifications

Size

Length	1.87 in [47.5 mm]
Width/Diameter	0.835 in [21.21 mm]
Height	0.75 in [19.05 mm]
Weight	0.0265 lbs [12.02 g]

Waveguide Interface

Waveguide Size	WR-28
Flange Type	Square Cover
Flange Designation	UG-599/U
Body Material and Plating	Anodized Aluminum

Environmental Specifications

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:



Features:


- Rectangular Waveguide Interface
- 26.5 GHz to 40 GHz
- 15 dBi Nominal Gain
- UG-599/U Square Cover Flange

Applications:

- Antenna Measurements
- Wireless Communication
- Laboratory Use
- Microwave Radio Systems

Fairview Microwave
 1130 Junction Dr. #100
 Allen, TX 75013
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Typical Performance Data




WR-28 Standard Waveguide Horn With UG-599/U Square Cover Flange and 15 dBi Nominal Gain Operating From 26.5 GHz to 40 GHz Frequency Range from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: [WR-28 Standard Waveguide Horn With UG-599/U Square Cover Flange and 15 dBi Nominal Gain Operating From 26.5 GHz to 40 GHz Frequency Range SH128-15](https://www.fairviewmicrowave.com/wr-28-waveguide-standard-gain-horn-0-db-ug-599-sh128-15-p.aspx)

URL: <https://www.fairviewmicrowave.com/wr-28-waveguide-standard-gain-horn-0-db-ug-599-sh128-15-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



WR28		
Dimension	Inches	mm
A	0.500	12.70
H (SQ.)	0.750	19.05
J	0.530	13.46
K (± 0.010)	0.280	7.11
L (± 0.010)	0.140	3.56
AA	0.116	2.95
AB	1.873	47.57
AC	0.615	15.62
AD	0.827	21.01
AE	0.039	0.99
AF	0.100	2.54
AG	0.300	7.62



STANDARD TOLERANCES

.X ± 0.2
.XX ± 0.1
.XXX ± 0.05

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

FAIRVIEW MICROWAVE INC.
ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].

TITLE WR-28 Standard Waveguide Horn With UG-599/U Square Cover Flange and 15 dBi Nominal Gain Operating From 26.5 GHz to 40 GHz Frequency Range	DWG NO SH128-15		CAGE CODE 3FKR5		
	CAD FILE 041417	SHEET	SCALE N/A	SIZE A	2233