


ATTENUATORS N 200 WATTS 3 GHZ

SA3N200-XX



SPECIFICATIONS

ELECTRICAL:

FREQUENCY: 0-3 GHZ
 IMPEDANCE: 50 OHMS
 VSWR @ 3 GHZ: 1.35 MAX
 POWER (AVG) 200 WATTS @ 25° C
 DERATED LINEARLY TO 20W @ 125° C
 POWER (PEAK) 10 KW
 5 μs PULSE WIDTH WITH 2% DUTY CYCLE

MATERIALS:

CONNECTORS: NICKEL PLATED BRASS
 CONTACTS: Au PLATED BeCu

ENVIRONMENTAL:

TEMP: -55 C TO +125 C

ROHS COMPLIANT

MALE IS INPUT; FEMALE IS OUTPUT

ATTENUATION ACCURACY (dB)			
10 dB	20 dB	30 dB	40 dB
±1.25	1.25	0.8	0.8

				FAIRVIEW MICROWAVE INC.			
				ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM			
				TITLE			
				ATTENUATORS N 200 WATTS 3 GHZ			
SIZE	CAGE CODE	DWG NO				REV	
A	3FKR5	SA3N200-XX				A	
SCALE						SHEET	