

# ATTENUATORS SMA M/F 6 GHZ

SA6-XX

## SPECIFICATIONS

### ELECTRICAL:

FREQUENCY: 0-6 GHZ


VSWR 1.20 MAX TO 6 GHZ

POWER (AVG) 2 WATTS @ 25 DEG C

IMPEDANCE: 50 OHMS

ATTENUATION ACCURACY:

|           |          |
|-----------|----------|
| 0-6 dB    | ± .3 dB  |
| 7-20 dB   | ± .5 dB  |
| 25, 30 dB | ± .75 dB |



### MECHANICAL:

MATERIAL BODY: PASSIVATED STAINLESS STEEL

MATERIAL RING & CONTACTS: BeCu

CENTER CONTACT: GOLD PLATED PER MIL-G-45204

RECOMMENDED TORQUE: 7-9 IN-LBS

### ENVIRONMENTAL:

TEMP: -55 C TO +125 C

ROHS COMPLIANT

**FAIRVIEW MICROWAVE INC.**

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

**ATTENUATORS SMA M/F 6 GHZ**

SIZE

**A**

CAGE CODE

**3FKR5**

DWG NO

**SA6-XX**

REV

--

SCALE

SHEET