

STT1843 DATA SHEET

RF Load 2 Watts To 18 GHz With Chain Tri-Metal Plated Brass TNC Male

RF termination (also called RF load or dummy load) STT1843 from Fairview Microwave operates from DC to 18 GHz and handles up to 2 Watts (CW). This TNC termination (or load) has a male gender. STT1843 TNC load termination offers 1.35:1 max VSWR.

RF terminations / loads are critical passive components in many RF, microwave and millimeter wave systems where signal reflection from unused ports can reduce the signal integrity and can potentially damage the device. By terminating an unused port with a matched load (dummy load), the incident energy will be absorbed with minimal reflection. These radio frequency termination components are commonly used to terminate devices such as couplers, circulators, and switches. Loads / terminations are also widely used in measurement systems to ensure accurate results. Fairview offers a large selection of in-stock RF, microwave and millimeter wave terminations up to 65 GHz with great performance over the entire operating range and with power handling capabilities up to 800 Watts (CW).

Electrical Specifications

Description	Min	Тур	Мах	Units
Frequency Range	DC		18	GHz
Impedance		50		Ohms
VSWR			1.35:1	
Input Power (CW)			2	Watts
derated linearly to 1W	at +125°C			

CONTRACTOR OF THE STATE

Features:

- DC to 18 GHz Frequency Range
- VSWR 1.35:1 Max
- Max Power 2 Watts (CW)
- TNC Male Coaxial Interface
- Includes Beaded Chain

Applications:

- Wireless
- SatCom
- Radar Systems
- Test and Measurement
- Commercial and Military
 Communication

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency Range	DC - 4	4 - 8	8 - 18			GHz
VSWR, Max	1.15:1	1.25:1	1.3 <mark>5:1</mark>			

Mechanical Specifications

Size	
Length	
Width	
Weight	

Configuration

Coni	nector
Hex	Size

1.1 in [27.94 mm] 0.63 in [16 mm] 0.0547 lbs [24.81 g]

TNC Male 14 mm

> Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com






Material Specifications

Housing Brass Tri-Metal Chain Passivated Stainless Steel Interce Certifications Chain Passivated Stainless Steel Interce Certifications Chain -55 to +125 deg C Interce Certifications Chain -55 to +125 deg C Interce Certifications Chain Yes Yes Chain Yes Yes	Description	Material	Plating
Brass Tri-Metal Coupling Nut Brass Tri-Metal Housing Brass Tri-Metal Housing Brass Tri-Metal Chain Passivated Stainless Steel Chain Passivated Stainless Steel Grommental Specifications -55 to +125 deg C Frieder Compliant Operating Range -55 to +125 deg C Frieder Compliant Passivated Stainless Yes Frieder Compliant REACH Compliant Yes Yes REACH Compliant 12/17/2015	Connector 1 Contact	Brass	
Coupling Nut Brass Tri-Metal Housing Brass Tri-Metal Housing Brass Tri-Metal Chain Passivated Stainless Steel Comperature -55 to +125 deg C Compliance Certifications Compliant Yes REACH Compliant 12/17/2015	nsulation	PTFE	
Housing Brass Tri-Metal Chain Passivated Stainless Steel Vironmental Specifications -55 to +125 deg C Operating Range -55 to +125 deg C mpliance Certifications (visit www.FairviewMicrowave.com for current of RoHS Compliant	3ody	Brass	Tri-Metal
Chain Passivated Stainless Steel	Coupling Nut	Brass	Tri-Metal
vironmental Specifications -55 to +125 deg C Operating Range -55 to +125 deg C mpliance Certifications (visit www.FairviewMicrowave.com for current RoHS Compliant Pes REACH Compliant 12/17/2015 REACH Compliant Yes REACH Compliant 12/17/2015	lousing	Brass	Tri-Metal
Temperature -55 to +125 deg C Operating Range -55 to +125 deg C npliance Certifications (visit www.FairviewMicrowave.com for current RoHS Compliant Yes REACH Compliant 12/17/2015 tted and Other Data Ited and Other Data	Chain	Passivated Stainless	Steel
	ROHS Compliant REACH Compliant ted and Other Dat	Yes 12/	

1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







Typical Performance Data

RF Load 2 Watts To 18 GHz With Chain Tri-Metal Plated Brass TNC Male from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: RF Load 2 Watts To 18 GHz With Chain Tri-Metal Plated Brass TNC Male STT1843

URL: https://www.fairviewmicrowave.com/rf-load-2-watts-18-ghz-chain-tnc-male-stt1843-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.







*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

DECIMAL .XX

.XXX

FAIRVIEW MICROWAVE INC.	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
TITLE RF Load 2 Watts To 18 GHz With Chain Tri-Metal Plated Brass TNC Male	DWG NO STT1843			CAGE CODE 3FKR5		
	CAD FILE 041316	SHEET	SCALE	N/A	SIZE A	3045

1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689