

ATTENUATORS N M/F 5 WATTS

SA6N5W-XX, SA12N5W-XX, SA18N5W-XX

SPECIFICATIONS

ELECTRICAL:

FREQ: SA6N5W: 6GHZ
 SA12N5W: 12.4GHZ
 SA18N5W: 18GHZ
 VSWR 1.2 MAX @ 6GHZ
 1.25 MAX @ 12.4GHZ
 1.4 MAX @ 18GHZ

POWER (AVG) 5 WATTS
 POWER (PEAK) 1 KW
 IMPEDANCE: 50 OHMS

ATTENUATION ACCURACY

1-2 DB +/- 0.4DB TO 12.4 GHZ, +/- 0.5DB TO 18GHZ
 3-10 DB +/- 0.3DB TO 18GHZ
 11-20 DB +/- 0.5DB TO 18GHZ
 30 DB +/- 1.0DB TO 18GHZ


MECHANICAL:

MATERIAL BODY: PASSIVATED STAINLESS STEEL
 CONTACTS: Au PLATED PER MIL-G-45204 BeCu

ENVIRONMENTAL:

TEMP: -55 C TO +125 C
 ROHS COMPLIANT

N-FEMALE



N-MALE

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

ATTENUATORS N M/F 5 WATTS

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SA6N5W, SA12N5W, SA18N5W	-
SCALE			SHEET