

ATTENUATORS N M/F 8GHZ 50W

SA8N50W-XX

SPECIFICATIONS


ELECTRICAL:

FREQUENCY: 0-8.5 GHZ
 VSWR 1.20 MAX @ 4GHZ
 VSWR 1.30 MAX @ 8.5GHZ
 POWER (AVG) 50 WATTS @ 25 DEG C
 POWER (PEAK) 1000 WATTS
 IMPEDANCE: 50 OHMS
 ATTENUATION ACCURACY:
 3-20DB +/- .75DB
 30-40DB +/- 1.0DB
 BIDIRECTIONAL

MECHANICAL:

MATERIAL CONNECTORS: PASSIVATED STAINLESS STEEL
 MATERIAL RING & CONTACTS: BeCu
 CENTER CONTACT: GOLD PLATED PER MIL-G-45204
 INTERFACE: MIL-STD-348B
 INSULATOR: TEFLON
 TEMP: -55 C TO +125 C

ROHS COMPLIANT



				FAIRVIEW MICROWAVE INC.	
				ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	
				TITLE	
				ATTENUATORS N M/F 8GHZ 50W	
SIZE	CAGE CODE	DWG NO	REV		
A	3FKR5	SA8N50W-XX	--		
SCALE			SHEET		