

10-32-M CONNECTOR  
RG174 RG316 CRIMP

SC5560

SPECIFICATIONS

ELECTRICAL:

FREQUENCY: 0-18 GHZ  
VSWR 1.3:1 MAX  
IMPEDANCE: 50 OHMS  
OP. TEMP RANGE: -55C- +155C




MECHANICAL:

MATERIAL BODY: Ni PLATED BRASS  
CENTER CONTACT: BRASS  
CONTACT PLATING: Au MIL-G-45204  
INSULATOR: TEFLON  
INTERFACE: MIL-STD-348A  
ROHS COMPLIANT


ASSEMBLY PROCEDURE

STRIP CABLE AS SHOWN,  
SLIDE ON CRIMP TUBE,  
INSTALL CABLE INTO CRIMP NUT ASSEMBLY,  
PUSH CABLE FORWARD UNTIL BOTTOMS OUT,  
SOFT SOLDER CENTER CONDUCTOR THRU SIDE HOLE,  
SLIDE CRIMP TUBE UP, CRIMP,  
THREAD COMPLETED ASSEMBLY INTO BODY,  
TIGHTEN

#10-32 UNEF-2B



STRIPPING DIMENSIONS



**FAIRVIEW MICROWAVE INC.**

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

10-32-M CONNECTOR RG174  
RG316 CRIMP

SIZE

A

CAGE CODE

3FKR5

DWG NO

SC5560

REV

A

SCALE

SHEET