

# ATTENUATORS N M/F 18GHZ

SA18N-XX

## SPECIFICATIONS

### ELECTRICAL:

FREQUENCY: 0-18 GHZ

VSWR

0-6 GHZ : 1.20:1 MAX

6-12 GHZ: 1.30:1 MAX

12-18GHZ 1.45:1 MAX

POWER (AVG) 2 WATTS @ 25 DEG C  
.5 WATTS @ 125 DEG C

POWER (PEAK) 250 WATTS

IMPEDANCE: 50 OHMS

ATTENUATION ACCURACY

+/- .3 DB 0-6 GHZ

+/- .5DB 6-18 GHZ

### MECHANICAL:

MATERIAL BODY: PASSIVATED S STEEL


MATERIAL RING & CONTACTS: BeCu

CENTER CONTACT: Au PLATED MIL-G-45204

### ENVIRONMENTAL:

TEMP: -65 C TO +125 C

ROHS COMPLIANT



<b>FAIRVIEW MICROWAVE INC.</b>			
ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM			
TITLE			
<b>ATTENUATORS N M/F 18GHZ</b>			
SIZE	CAGE CODE	DWG NO	REV
<b>A</b>	<b>3FKR5</b>	<b>SA18N-XX</b>	<b>B</b>
SCALE		SHEET	