

# SMA F'S ISOLATOR 1.7-2.4 GHZ

SFI1724S

## SPECIFICATIONS

### ELECTRICAL

FREQUENCY: 1.7-2.4 GHZ  
 IMPEDANCE: 50 OHMS  
 VSWR: 1.3:1  
 INSERTION LOSS: 0.5 DB  
 AVG POWER: 10 W FORWARD @ CW  
 AVG POWER: 1 W REVERSE @ CW  
 ISOLATION: 20 DB


### MECHANICAL

MATERIAL CONNECTORS: Au PLATED STAINLESS STEEL  
 MATERIAL CONTACTS: Au PLATED BeCu

OPERATING TEMPERATURE: 25°C

ROHS COMPLIANT

DIRECTION: FROM LEFT TO RIGHT



**FAIRVIEW MICROWAVE INC.**

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

**SMA F'S ISOLATOR 1.7-2.4 GHZ**

SIZE	CAGE CODE	DWG NO	REV
<b>A</b>	<b>3FKR5</b>	<b>SFI1724S</b>	--

SCALE	SHEET
-------	-------