

ATTENUATORS SMA M/F 18GHZ 50W

SA18S50W-XX

SPECIFICATIONS

ELECTRICAL:

FREQUENCY: 0-18 GHZ

VSWR 1.20 MAX TO 8 GHZ

1.25MAX TO 12 GHZ

1.35 MAX TO 18 GHZ

VSWR FOR ONLY 6 DB 1.45 MAX TO 18 GHZ

POWER (AVG) 50 WATTS @ 25 DEG C

POWER (PEAK) 1000 WATTS

IMPEDANCE: 50 OHMS

ATTENUATION ACCURACY: +1.5, -.5

BIDIRECTIONAL

MECHANICAL:

MATERIAL CONNECTORS: PASSIVATED STAINLESS STEEL

MATERIAL RING & CONTACTS: BeCu

CENTER CONTACT: GOLD PLATED PER MIL-G-45204


INTERFACE: MIL-STD-348B

INSULATOR: TEFLON

RECOMMENDED TORQUE: 7-8.5 IN-LBS

TEMP: -55 C TO +125 C

BIDIRECTIONAL



FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

ATTENUATORS SMA M/F 18GHZ 50W

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SA18S50W-XX	A
SCALE	SHEET		