

2.4-2.4mm F/F FLANGE ADAPTER

SM3017

SPECIFICATIONS

ELECTRICAL


FREQUENCY: 0-50 GHZ
 IMPEDANCE: 50 OHMS
 VSWR: 1.3:1 MAX

MECHANICAL

500 CYCLES MIN
 4 IN-OUNCES MIN CONTACT TORQUE
 8-10 IN-LBS COUPLING NUT MATING TORQUE
 DURABILITY: 500 CYCLES MIN.
 TEMPERATURE RANGE: -55 TO +100 DEG C

MATERIALS

BODY PASS STAINLESS STEEL
 CONTACTS Au PLATING



				FAIRVIEW MICROWAVE INC.	
				ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	
				TITLE	
				2.4-2.4mm F/F FLANGE ADAPTER	
SIZE		CAGE CODE	DWG NO		REV
A			SM3017		--
SCALE			SHEET		