

2.4mm SWEPT 50GHZ ADAPTER

SM3027


SPECIFICATIONS

ELECTRICAL
 50 OHMS
 VSWR 1.30:1 MAX
 FREQUENCY: 0-50 GHZ

MECHANICAL
 500 CYCLES MIN
 4.0 INCH-OUNCES MIN CONTACT TORQUE
 8-10 LBS COUPLING NUT MATING TORQUE

ENVIRONMENTAL
 -55 DEG C TO +100 DEG C
 CORROSION: MIL-STD 202
 VIBRATION: MIL-STD 202

MATERIALS PASSIVATED STAINLESS STEEL
 BODY: SST ASTM A484 / A582
 BeCu ATSM-B-196
 PASSIVATED ASTM A380
 CENTER CONTACTS Au PLATED
 MIL-G-45204



				FAIRVIEW MICROWAVE INC.	
				ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	
				TITLE SM5260	
				2.4mm SWEPT 50GHZ ADAPTER	
SIZE	CAGE CODE	DWG NO		REV	
A	3FKR5	SM3027		C	
SCALE			SHEET		