

# ATTENUATORS SMA M/F 3 GHZ

SA3015-XX

## SPECIFICATIONS

### ELECTRICAL:


FREQUENCY: 0-3 GHZ  
 VSWR 1.20 MAX TO 3 GHZ  
 POWER (AVG) 2 WATTS @ 25° C  
 POWER (PEAK) 200 WATTS  
 POWER DERATES LINEARLY <10% @ 125° C  
 IMPEDANCE: 50 OHMS

### MECHANICAL:

MATERIAL BODY: PASSIVATED STAINLESS STEEL  
 MATERIAL RING & CONTACTS: BeCu  
 CENTER CONTACT: GOLD PLATED PER MIL-G-45204  
 RECOMMENDED TORQUE: 7-9 IN-LBS

### ENVIRONMENTAL:

TEMP: -55 C TO +125 C  
 ROHS COMPLIANCE



				<b>FAIRVIEW MICROWAVE INC.</b>	
				ALLEN, TX 75013 <a href="http://WWW.FAIRVIEWMICROWAVE.COM">WWW.FAIRVIEWMICROWAVE.COM</a>	
				TITLE	
				ATTENUATORS SMA M/F 3 GHZ	
SIZE		CAGE CODE	DWG NO	REV	
<b>A</b>		<b>3FKR5</b>	<b>SA3015-XX</b>	<b>--</b>	
SCALE			SHEET		