

# 2.4mm - 3.5mm ADAPTERS 34GHZ

SM3060, SM3065, SM3070, SM3075





## SPECIFICATIONS

**ELECTRICAL**  
 50 OHMS  
 VSWR 1.25:1 MAX @ 34GHZ  
 FREQUENCY: 0-34 GHZ

**MECHANICAL**  
 500 CYCLES MIN  
 4.0 INCH-OUNCES MIN CONTACT TORQUE  
 8-10 LBS COUPLING NUT MATING TORQUE

**ENVIRONMENTAL**  
 -65 DEG C TO +85 DEG C  
 CORROSION: MIL-STD 202  
 VIBRATION: MIL-STD 202

**MATERIALS** PASSIVATED STAINLESS STEEL  
 BODY: SST ASTM A484 / A582  
 BeCu ATSM-B-196  
 PASSIVATED ASTM A380  
 CENTER CONTACTS Au PLATED  
 MIL-G-45204



**FAIRVIEW MICROWAVE INC.**  
 ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE  
**2.4mm - 3.5mm ADAPTERS 34GHZ**

SIZE <b>A</b>	CAGE CODE	DWG NO SM3060, SM3065, SM3070, SM3075	REV <b>A</b>
SCALE		SHEET	