

# ATTENUATOR 2.92 M/F 40GHZ 2 WATTS

SA4016-XX

## SPECIFICATIONS



### ELECTRICAL:

FREQUENCY: 0-40 GHZ  
 VSWR @ 18 GHZ: 1.30:1 MAX  
 VSWR @ 40 GHZ: 1.40:1 MAX  
 POWER (AVG) 2 WATT @ 25°C,  
 POWER DERATES LINEARLY 0.2W @ 125°C  
 IMPEDANCE: 50 OHMS  
 ATTENUATION ACCURACY:  
 +/- .8 DB 0-26GHZ  
 +/- 1DB 40 GHZ

### MECHANICAL:

MATERIAL BODY: PASSIVATED STAINLESS STEEL  
 MATERIAL CONTACTS: BeCu  
 CENTER CONTACT: GOLD PLATED PER MIL-G-45204  
 TEMP: -65°C TO +125°C

ROHS COMPLIANT



|          |           |   |     |       |
|----------|-----------|---|-----|-------|
|          |           | <b>FAIRVIEW MICROWAVE INC.</b>            |     |       |
|          |           | ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM |     |       |
|          |           | TITLE                                     |     |       |
|          |           | ATTENUATOR 2.92 M/F 40GHZ 2 WATTS         |     |       |
| SIZE     | CAGE CODE | DWG NO                                    | REV |       |
| <b>A</b> | 3FKR5     | <b>SA4016-XX</b>                          | --  |       |
| SCALE    |           |   |     | SHEET |