

2.92 M/F ATTENUATOR 40GHZ 5 WATTS

SA4017-XX

SPECIFICATIONS

ELECTRICAL:

FREQUENCY: 0-40 GHZ
 VSWR @ 18 GHZ: 1.20:1 MAX
 VSWR @ 40GHZ: 1.35:1 MAX
 POWER (AVG) 5 WATTS @ 25° C;
 DERATES LINEARLY TO 0.5W @ 125° C
 POWER (PEAK) 200 WATTS
 IMPEDANCE: 50 OHMS
 ATTENUATION ACCURACY:
 +/- .8DB 0-18GHZ
 +/- 1.5DB 18-40GHZ


MECHANICAL:

MATERIAL BODY: PASSIVATED STAINLESS STEEL
 MATERIAL CONTACTS: BeCu
 CONTACT MATERIAL: BeCu (F), BRASS (M)
 CONTACT PLATING: Au PER MIL-G-45204

ENVIRONMENTAL:

TEMP: -55° C TO +125° C

ROHS COMPLIANT



				FAIRVIEW MICROWAVE INC.			
				ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM			
				TITLE			
				2.92 M/F ATTENUATOR 40GHZ 5 WATTS			
SIZE		CAGE CODE		DWG NO		REV	
A				SA4017-XX		A	
SCALE				SHEET			