

ATTENUATORS N 50 WATTS 4 GHZ

SA4N508-XX

SPECIFICATIONS

ELECTRICAL:

FREQUENCY: 0-4 GHZ
 VSWR @ 4 GHZ: 1.35 MAX
 IMPEDANCE: 50 OHMS
 POWER (AVG) 50 WATTS @ 25° C
 DERATED LINEARLY TO 5W @ 125° C
 POWER (PEAK) 10 KW
 5 μs PULSE WIDTH WITH 0.5% DUTY CYCLE

ATTENUATION ACCURACY				
1-9 dB	10 dB	20 dB	30 dB	40 dB
±0.75	±0.75	±0.75	±0.75	±0.75


MATERIALS:

CONNECTORS: NICKEL PLATED BRASS
 CONTACTS: Au PLATED BeCu

ENVIRONMENTAL:

TEMP: -55 C TO +125 C

ROHS COMPLIANT



Dimensions In inches (mm) TYPICAL		FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM		
		TITLE ATTENUATORS N 50 WATTS 4 GHZ		
SIZE	CAGE CODE	DWG NO	REV	
A	3FKR5	SA4N508-XX	B	
SCALE		SHEET		