

3.5mm - SMA ADAPTERS 27GHZ

SM3325, SM3328, SM3331, SM3334





SPECIFICATIONS

ELECTRICAL
 50 OHMS
 VSWR 1.20:1 MAX @ 27GHZ
 FREQUENCY: 0-27 GHZ

MECHANICAL
 500 CYCLES MIN
 4.0 INCH-OUNCES MIN CONTACT TORQUE
 8-10 LBS COUPLING NUT MATING TORQUE

ENVIRONMENTAL
 -65 DEG C TO +85 DEG C
 CORROSION: MIL-STD 202
 VIBRATION: MIL-STD 202

MATERIALS PASSIVATED STAINLESS STEEL
 BODY: SST ASTM A484 / A582
 BeCu ATSM-B-196
 PASSIVATED ASTM A380
 CENTER CONTACTS Au PLATED
 MIL-G-45204



				FAIRVIEW MICROWAVE INC.			
				ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM			
				TITLE			
				3.5mm - SMA ADAPTERS 27GHZ			
SIZE	CAGE CODE	DWG NO		REV			
A		SM3325, SM3328, SM3331, SM3334		A			
SCALE			SHEET				