

ATTENUATORS N M/F 6 GHZ

SA6021-XX

SPECIFICATIONS

ELECTRICAL:


FREQUENCY: 0-6 GHZ
 VSWR @ 2GHZ : 1.10 MAX
 VSWR @ 4GHZ : 1.15 MAX
 VSWR @ 6GHZ : 1.20 MAX
 POWER (AVG) 2 WATTS
 IMPEDANCE: 50 OHMS
 ATTENUATION ACCURACY
 ±0.5 DB FROM DC-6 GHZ

MECHANICAL:

MATERIAL BODY: BRASS
 PLATING: NICKEL 50μ
 MATERIAL CONTACT: PHOSPHOR BRONZE
 MATERIAL CONTACT PLATING Au 30μ
 INSULATOR: TEFLON

ENVIRONMENTAL:

TEMP: -55°C TO +155°C
 ROHS COMPLIANT



| | | | | | |
|----------|--------------|--------|------------------|---|--|
| | | | | FAIRVIEW MICROWAVE INC. | |
| | | | | ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM | |
| | | | | TITLE | |
| | | | | ATTENUATORS N M/F 6 GHZ | |
| SIZE | CAGE CODE | DWG NO | SA6021-XX | | |
| A | 3FKR5 | | | | |
| SCALE | | | SHEET | | |
| | | | REV -- | | |