

2.92mm - 3.5mm ADAPTERS 34GHZ

SM3367, SM3370, SM3373, SM3376

SPECIFICATIONS

ELECTRICAL

50 OHMS
 VSWR 1.15:1 MAX @ 34 GHZ
 FREQUENCY: 0-34 GHZ

MECHANICAL





500 CYCLES MIN
 4.0 INCH-OUNCES MIN CONTACT TORQUE
 8-10 LBS COUPLING NUT MATING TORQUE

ENVIRONMENTAL

-65 DEG C TO +85 DEG C
 CORROSION: MIL-STD 202
 VIBRATION: MIL-STD 202

MATERIALS PASSIVATED STAINLESS STEEL

BODY: SST ASTM A484 / A582
 BeCu ATSM-B-196
 PASSIVATED ASTM A380
 CENTER CONTACTS Au PLATED
 MIL-G-45204



				FAIRVIEW MICROWAVE INC.			
				ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM			
				TITLE			
				2.92mm - 3.5mm ADAPTERS 34GHZ			
SIZE		CAGE CODE		DWG NO		REV	
A				SM3367, SM3370, SM3373, SM3376		B	
SCALE				SHEET			