

# SMA M/F 6 GHZ 10W ATTENUATORS

SA6S10W-XX

## SPECIFICATIONS

### ELECTRICAL:

FREQUENCY: 0-6 GHZ

VSWR 1.15 MAX TO 3 GHZ

1.20 MAX TO 6 GHZ

POWER (AVG) 10 WATTS @ 25 DEG C

IMPEDANCE: 50 OHMS

ATTENUATION ACCURACY:

1-10 dB	±.5 dB
20 dB	±.7 dB
30 dB	±1.0 dB

### MECHANICAL:

MATERIAL CONNECTORS: PASSIVATED STAINLESS STEEL

MATERIAL RING & CONTACTS: BeCu


CENTER CONTACT: GOLD PLATED PER MIL-G-45204

RECOMMENDED TORQUE: 7-9 IN-LBS

### ENVIRONMENTAL:

TEMP: -55 C TO +125 C

ROHS COMPLIANT



				<b>FAIRVIEW MICROWAVE INC.</b>			
				ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM			
				TITLE			
				<b>SMA M/F 6 GHZ 10W ATTENUATORS</b>			
SIZE		CAGE CODE		DWG NO		REV	
<b>A</b>		<b>3FKR5</b>		<b>SA6S10W-XX</b>		--	
SCALE				SHEET			