

SPECIFICATIONS

RETURN LOSS

- 28 DB MIN @ 2 GHZ
- 26 DB MIN @ 4 GHZ
- 23 DB MIN @ 8 GHZ
- 20 DB MIN @ 12 GHZ
- 18 DB MIN @ 18 GHZ

VELOCITY OF PROPAGATION: 69.5 %
 CAPACITANCE: 26.5 pF/ft
 SHIELDING EFFECTIVENESS: 90 DB MIN


CONNECTORS:

- MATERIAL BODY: PASSIVATED STAINLESS STEEL
- CONTACTS: BeCu
- CONTACT PLATING: Au MIL-G-45204
- DIELECTRIC: TEFLON
- INTERFACE: MIL-STD-348A

CABLE DIELECTRIC: SOLID PTFE
 CABLE JACKET: FEP, BLUE

TEMPERATURE RANGE: -30° C to +105°C

RoHS COMPLIANT



				FAIRVIEW MICROWAVE INC.	
				ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	
				TITLE	
				SMA FLEXABLE CABLES 18 GHZ WITH STAINLESS STEEL CONNECTORS	
SIZE		CAGE CODE	DWG NO		REV
A		3FKR5	SCA1814-0101-XX		--
SCALE					SHEET