



# RF Load 2 Watts To 2 GHz Tri-Metal Plated Brass BNC Male

RF termination (also called RF load or dummy load) ST2B from Fairview Microwave operates from DC to 2 GHz and handles up to 2 Watts (CW). This BNC termination (or load) has a male gender. ST2B BNC load termination offers 1.15:1 max VSWR.

RF terminations / loads are critical passive components in many RF, microwave and millimeter wave systems where signal reflection from unused ports can reduce the signal integrity and can potentially damage the device. By terminating an unused port with a matched load (dummy load), the incident energy will be absorbed with minimal reflection. These radio frequency termination components are commonly used to terminate devices such as couplers, circulators, and switches. Loads / terminations are also widely used in measurement systems to ensure accurate results. Fairview offers a large selection of in-stock RF, microwave and millimeter wave terminations up to 65 GHz with great performance over the entire operating range and with power handling capabilities up to 800 Watts (CW).



Description	Min	Тур	Max	Units
Frequency Range	DC		2	GHz
Impedance		50		Ohms
VSWR			1.15:1	
Input Power (CW)			2	Watts
derated linearly to 1W at +125°C				
Input Power (Peak)			1	KWatts
50 µsec duration				



## **Features:**

- DC to 2 GHz Frequency Range
- VSWR 1.15:1 Max
- Max Power 2 Watts (CW)
- BNC Male Coaxial Interface

# **Applications:**

- Wireless
- SatCom
- Radar Systems
- Test and Measurement
- Commercial and Military Communication

#### **Mechanical Specifications**

Size

Length Width Weight 1.14 in [28.96 mm] 0.58 in [14.73 mm] 0.0388 lbs [17.6 g]

Configuration

Connector Specification

BNC Male MIL-STD-348

#### **Material Specifications**

Description	Material	Plating	
Connector 1 Contact		Gold	
Insulation	PTFE		
Body	Brass	Tri-Metal	
Coupling Nut	Brass	Tri-Metal	
Housing	Brass	Tri-Metal	

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013

Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





## **Environmental Specifications**

**Temperature** 

Operating Range -55 to +125 deg C

Compliance Certifications (visit www.FairviewMicrowave.com for current document)


RoHS Compliant Yes

REACH Compliant 12/17/2015

#### **Plotted and Other Data**

Notes:

### **Typical Performance Data**



RF Load 2 Watts To 2 GHz Tri-Metal Plated Brass BNC Male from Fairview Microwave is in-stock and available to ship sameday. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: RF Load 2 Watts To 2 GHz Tri-Metal Plated Brass BNC Male ST2B

URL: https://www.fairviewmicrowave.com/rf-load-2-watts-2-ghz-bnc-male-st2b-p.aspx


The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

Copyright © 2016







FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES:  1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  3. DIMENSIONS ARE IN INCHES [mm].					
RF Load 2 Watts To 2 GHz Tri-Metal Plated Brass BNC	DWG NO ST2B			CAGE CODE 3FKR5		
Male	CAD FILE 041316	SHEET	SCALE	E N/A	SIZE A	3045