


LTR	DESCRIPTION	DATE	BY
-	Released	11/12/96	JCL
A	Redesign Nut and Back Body	11/9/05	JCL



**I. MATERIALS & FINISHES**

- center contact: Gold Plated Beryllium Copper
- outer contact: Albaloy Plated Brass
- body: Albaloy Plated Brass
- coupling nut: Albaloy Plated Brass
- crimp sleeve: Silver Plated Copper
- dielectric: Teflon® PTFE
- gasket: Silicone Rubber
- shrink sleeve: Adhesive Lined Polyolefin
- crimp size: .429" hex

**II. ELECTRICAL PROPERTIES**

- impedance: 50 ohms
- working voltage: 1000 vrms (max)
- vswr: 1.25:1 (max) up to 3GHz
- insertion loss: 0.1 x √Fghz

Unless otherwise specified, dimensions are in inches. Tolerances are applicable when specified.

These drawings and specifications contain proprietary information which is the property of Times Microwave Systems.

Approvals		
Drawn	JCL	11/12/96
Check		
Prj. Mgr.		
Prd. Mgr.		
QA Mgr.		



**TIMES MICROWAVE SYSTEMS**

Wallingford, CT 06492  
 (203) 949-8400; (203) 949-8423.Fax  
 www.timesmicrowave.com

**EZ-400-NMH-D**

Type N Male (plug) – Non-solder pin  
 for LMR-400 Cable Type(s)

Size A	CAGE CODE <b>68999</b>	Drawing No.: <b>3190-400</b>
--------	---------------------------	---------------------------------