

HYBRID 700-2700MHZ N-F'S 90 DEGREES

SH3725


SPECIFICATIONS

ELECTRICAL

FREQUENCY: 700-2700MHZ
PIM <140dBc (2 tones @ +43dBm)
COUPLING; 3DB NOMINAL
POWER: 120W AVG, 1.5KW PEAK
IMPEDANCE: 50 OHMS
VSWR: 1.20:1 MAX , ALL PORTS
AMPLITUDE BALANCE: 0.15DB
LOSS: 3.2 DB MAX (3+.2)
ISOLATION: 30 DB MIN 700-2200;
25DB MIN 2200-2700

MECHANICAL

MATERIALS BODY: PASSIVATED ALUMINUM
CONNECTORS: N-FEMALE, SILVER PLATING
TEMP RANGE: -35 TO +65 DEG C
WEIGHT: 14 oz



				FAIRVIEW MICROWAVE INC.			
				ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM			
				TITLE			
				HYBRID 700-2700MHZ N-F'S 90 DEGREES			
SIZE	CAGE CODE	DWG NO		REV			
A	3FKR5	SH3725		B			
SCALE				SHEET			