

# 2.92mm - SMA ADAPTERS 27GHZ

SM3275, SM3280, SM3285, SM3290





## SPECIFICATIONS

**ELECTRICAL**  
 50 OHMS  
 VSWR 1.20:1 MAX @ 27GHZ  
 FREQUENCY: 0-27 GHZ

**MECHANICAL**  
 500 CYCLES MIN  
 4.0 INCH-OUNCES MIN CONTACT TORQUE  
 8-10 LBS COUPLING NUT MATING TORQUE

**ENVIRONMENTAL**  
 -65 DEG C TO +85 DEG C  
 CORROSION: MIL-STD 202  
 VIBRATION: MIL-STD 202

**MATERIALS** PASSIVATED STAINLESS STEEL  
 BODY: SST ASTM A484 / A582  
 BeCu ATSM-B-196  
 PASSIVATED ASTM A380  
 CENTER CONTACTS Au PLATED  
 MIL-G-45204



**FAIRVIEW MICROWAVE INC.**

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

**2.92mm - SMA ADAPTERS 27GHZ**

SIZE	CAGE CODE	DWG NO	REV
<b>A</b>	<b>3FKR5</b>	<b>SM3275, SM3280, SM3285, SM3290</b>	<b>B</b>

SCALE	SHEET
-------	-------