

# SMA/F-BNC/F FLANGE 4GHZ ADAPTER

SM4708

## SPECIFICATIONS


### ELECTRICAL

FREQUENCY: 0-4 GHZ  
 IMPEDANCE: 50 OHMS  
 VSWR: 1.20:1 MAX  
 VRMS: 250 V SEA LEVEL

### MECHANICAL

MATERIALS BODY SMA: PASS. STAINLESS STEEL  
 MATERIALS BODY BNC: NICKEL PLATED BRASS  
 MATERIAL CONTACTS: BeCu  
 CONTACT PLATING: Au PER MIL-G-45204  
 INSULATOR: TEFLON  
 INTERFACE: MIL-STD-348B  
 TEMPERATURE RANGE: -55 TO +125°C

ROHS COMPLIANT



				<b>FAIRVIEW MICROWAVE INC.</b>	
				ALLEN, TX 75013 <a href="http://WWW.FAIRVIEWMICROWAVE.COM">WWW.FAIRVIEWMICROWAVE.COM</a>	
				TITLE	
				<b>SMA/F-BNC/F FLANGE 4GHZ ADAPTER</b>	
		SIZE	CAGE CODE	DWG NO	REV
		<b>A</b>	<b>3FKR5</b>	<b>SM4708</b>	<b>C</b>
				SCALE	SHEET