

SMA/ M - SMA/F REV POLARITY

SM4975

SPECIFICATIONS


ELECTRICAL
 50 OHMS
 VSWR 1.20:1 MAX @ 18 GHZ
 FREQUENCY: 0-18 GHZ

MECHANICAL
 500 CYCLES MIN
 3.0 INCH-OUNCES MIN CONTACT TORQUE
 7-9 LBS COUPLING NUT MATING TORQUE

ENVIRONMENTAL
 -55 DEG C TO +135 DEG C
 CORROSION: MIL-STD 202
 VIBRATION: MIL-STD 202

MATERIALS PASSIVATED STAINLESS STEEL
 BODY: SST ASTM A484 / A582
 BeCu ATSM-B-196
 PASSIVATED ASTM A380
 CENTER CONTACTS Au PLATED 50μ"
 MIL-G-45204

ROHS COMPLIANT



				FAIRVIEW MICROWAVE INC.			
				ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM			
				TITLE			
				SMA/ M - SMA/F REV POLARITY			
SIZE	CAGE CODE	DWG NO		REV			
A	3FKR5	SM4975		---			
SCALE			SHEET				