



REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	4/6/2022	K. HIETPAS



400 SERIES, 50 OHM LOW-LOSS COAXIAL CABLE
 JACKET: POLYETHYLENE, BLACK; NOM. DIA.: .40" [10.16]
 OPERATING TEMPERATURE RANGE: -40 °C TO +85 °C.
 [SEE CA-400 FOR REF.]



THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS, DIVERSION CONTRARY TO U.S. LAW PROHIBITED.



UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES
 DIMENSIONS IN [] ARE MILLIMETERS
 TOLERANCES:
 CABLE LENGTH (L) TOLERANCES:

THIRD-ANGLE PROJECTION
 THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRVIEW MICROWAVE CORPORATION. ALL RIGHTS RESERVED.

SIZE	GAGE CODE	FRACTIONS	FRACTIONS	ANGLES ± 1°
A	3FKRS	X = ±.2 [5.08]	12 [305] < L ≤ 60 [1524] = ±2 [51] / -0	120 [3048] < L ≤ 300 [7620] = ±6 [152] / -0
		XX = ±.02 [.51]	60 [1524] < L ≤ 120 [3048] = ±4 [102] / -0	300 [7620] < L = +5%L / -0
		XXX = ±.005 [.13]	120 [3048] < L ≤ 300 [7620] = ±6 [152] / -0	

SCALE	SHEET	OF
N/A	1	1

ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.

SIZE	GAGE CODE	DRAWN BY	ITEM NO.	REV
A	3FKRS	K.DANG	FMANKIT1000	A