

REVISIONS							
REV.	DESCRIPTION	DATE	APPROVED				
A	INITIAL RELEASE	4/6/2022	K. HIETPAS				
THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.							
Fairview Microwave™ an INFINITE brand							
<p>UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS</p> <p>TOLERANCES:</p> <table border="1"> <tr> <td>$X = \pm 2$ $XX = \pm .02$ $XXX = \pm .005$</td> <td>$[5.08]$ $.51$ $.13$</td> <td>FRACTIONS $\pm .125$ 60 120 300 300</td> <td>$1 \leq 12 [305] = +1[25] / -0$ $12 [305] < L \leq 1524 = +2 [51] / -0$ $60 [1524] < L \leq 120 [305] = +4 [102] / -0$ $120 [3048] < L \leq 300 [7620] = +6 [152] / -0$ $300 [7620] < L = +5%L / -0$</td> </tr> </table> <p>COAX-SEAL® Seals Connectors from Moisture</p> <p>RP SMA PLUG CRIMP CONNECTOR</p> <p>400 SERIES, 50 OHM LOW-LOSS COAXIAL CABLE JACKET: POLYETHYLENE, BLACK; NOM. DIA: .40" [10.16] OPERATING TEMPERATURE RANGE: -40°C TO +85°C. (SEE CA-400 FOR REF.)</p> <p>2X SHRINK TUBING BLACK</p> <p>10 FEET</p> <p>ANTENNA SHOWN WITHOUT MOUNTING HARDWARE</p> <p>N-FEMALE CONNECTOR</p> <p>Φ 1.0 [25]</p> <p>3.9 [100]</p> <p>3.5 [90]</p> <p>4.6 [117]</p> <p>3.2 [80]</p> <p>MOUNTING HARDWARE INCLUDED</p> <p>ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.</p> <p>SCALE N/A</p> <p>SIZE A</p> <p>CAGE CODE 3FKR5</p> <p>DRAWN BY K.DANG</p> <p>ITEM NO. FMANKIT1001</p> <p>REV A</p>				$X = \pm 2$ $XX = \pm .02$ $XXX = \pm .005$	$[5.08]$ $.51$ $.13$	FRACTIONS $\pm .125$ 60 120 300 300	$1 \leq 12 [305] = +1[25] / -0$ $12 [305] < L \leq 1524 = +2 [51] / -0$ $60 [1524] < L \leq 120 [305] = +4 [102] / -0$ $120 [3048] < L \leq 300 [7620] = +6 [152] / -0$ $300 [7620] < L = +5%L / -0$
$X = \pm 2$ $XX = \pm .02$ $XXX = \pm .005$	$[5.08]$ $.51$ $.13$	FRACTIONS $\pm .125$ 60 120 300 300	$1 \leq 12 [305] = +1[25] / -0$ $12 [305] < L \leq 1524 = +2 [51] / -0$ $60 [1524] < L \leq 120 [305] = +4 [102] / -0$ $120 [3048] < L \leq 300 [7620] = +6 [152] / -0$ $300 [7620] < L = +5%L / -0$				