



REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	03/1/2022	TGALLA



HYBRID D-SUB 7-PIN, MALE		SPECIFICATIONS	
PIN #	DESCRIPTION		
A1	VDD	28 VDC	
A2	GND	Ground	
1	SHUTDOWN	Amplifier Disable: TTL Logic High (3.3V) (Intemally PulledLow)	
2	CURRENT MONITOR	Andlog voltage relative to IDD @ 100mV per Ampere	
3	TEMP MONITOR	Andlog voltage relative to Module's Temperature @ 10 mV/°C	
4	GND	Ground	
5	NC	No connection	



VIEW A-A

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS, DIVERSION CONTRARY TO U.S. LAW PROHIBITED.



TOLERANCES:		THIRD-ANGLE PROJECTION	
UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES			
DIMENSIONS IN [] ARE MILLIMETERS			
CABLE LENGTH (L) TOLERANCES:			
L ≤ 1/2 (806) = +1 [25] / -0			
1/2 (1305) < L ≤ 60 [1524] = +2 [51] / -0			
60 [1524] < L ≤ 120 [3048] = +4 [102] / -0			
120 [3048] < L ≤ 300 [7620] = +6 [152] / -0			
300 [7620] < L = +5%L / -0			
X = ±.2 [5.08] FRACTIONS			
XX = ±.02 [.51] ±.1/32			
XXX = ±.005 [.13] ANGLES ± 1°			
ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.			
SCALE			
1			

THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRVIEW MICROWAVE CORPORATION. ALL RIGHTS RESERVED.

SIZE	GAGE CODE	DRAWN BY	ITEM NO.	SCALE	REV
A	3FKR5	BPUCHASKI	FMAM5109	N/A	A