

6

5

4

3

2

1

REVISION

ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	03/03/2025	HBAKKE	KHIETPAS

F

F

E

E

D

D

C


C

B

B

A

A



UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:

$X = \pm .2$ [5]	FRACTIONS $\pm 1/32$
$XX = \pm .02$ [0.5]	
$XXX = \pm .005$ [0.13]	ANGLES $\pm 1^\circ$

CABLE LENGTH TOLERANCES:

≤ 12 [305] = $+1$ [25] / -0
> 12 [305] ≤ 60 [1524] = $+2$ [51] / -0
> 60 [1524] ≤ 120 [3048] = $+4$ [102] / -0
> 120 [3048] ≤ 300 [7620] = $+6$ [152] / -0
> 300 [7620] = $+5\%$ / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY
AND SUBJECT TO CHANGE WITHOUT NOTICE.
UN-DIMENSIONED/NON-CRITICAL FEATURES
MAY VARY IN SIZE AND COLOR
COLORS MAY VARY

 **Fairview Microwave®**
an INFINIT® brand

Website: www.FairviewMicrowave.com
Phone: 1.800.715.4396 | 1.972.649.6678



INTERPRET ALL DIMENSIONS AND
TOLERANCES PER ASME Y14.5

SCALE
NONE

SHEET
1 OF 1

DESCRIPTION
144 / 430MHz, 2.15 / 3.5 dBi, ANTENNA, SMA MALE

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	3FKR5	HBAKKE	FMANRBD1073	A

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.