


REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	06/07/22	AGANWANI



STRIPPING DIMENSIONS

5/8 - 24 UNEF - 2A

ASSEMBLY PROCEDURES

1. TRIM CABLE JACKET & DIELECTRIC TO DIMENSIONS AS SHOWN, POINT CENTER CONDUCTOR.
2. PLACE WASHER THROUGH CENTER CONDUCTOR.
3. INSERT CABLE INTO BODY UNTIL BOTTOMS OUT. SOLDER OUTER CONDUCTOR TO BODY.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS, DIVERSION CONTRARY TO U.S. LAW PROHIBITED.



TITLE

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS		THIRD-ANGLE PROJECTION	
TOLERANCES:		THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRVIEW MICROWAVE CORPORATION. ALL RIGHTS RESERVED.	
X = ±.2	[.008]	FRACTIONS	±.1/32
XX = ±.02	[.51]	ANGLES	± 1°
XXX = ±.005	[.13]	CABLE LENGTH (L) TOLERANCES:	
ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.		L ≤ 12 [305]	±.1 [25] /-.0
SIZE		12 [305] < L ≤ 60 [1524]	±.2 [51] /-.0
GAGE CODE		60 [1524] < L ≤ 120 [3048]	±.4 [102] /-.0
3FKRS		120 [3048] < L ≤ 300 [7620]	±.6 [152] /-.0
DRAWN BY		300 [7620] < L	±.9% /-.0
VTHANGARAJ		SCALE	
ITEM NO.		N/A	
FMCN1905		REV	
REV		A	