



| REVISIONS |                 |         |          |
|-----------|-----------------|---------|----------|
| REV.      | DESCRIPTION     | DATE    | APPROVED |
| A         | INITIAL RELEASE | 7/30/21 | SRAUTUS  |



- NOTES:
1. CABLES 84" AND UNDER HAVE 1 LABEL CENTERED. CABLES OVER 84" HAVE 2 LABELS, ONE AT EACH END 12" FROM THE FRONT OF THE CONNECTOR.
  2. PIM LABEL 6" FROM CABLE END 1 PLACE.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS, DIVERSION CONTRARY TO U.S. LAW PROHIBITED.



|   |                 |   |                   |       |   |  |
|---|-----------------|---|-------------------|-------|---|--|
| UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES<br>DIMENSIONS IN [ ] ARE MILLIMETERS |                 |   |                   |       | THIRD ANGLE PROJECTION<br>       |  |
| TOLERANCES:   |                 |   |                   |       | THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRVIEW MICROWAVE CORPORATION. ALL RIGHTS RESERVED. |  |
| CABLE LENGTH (L) TOLERANCES:  |                 |   |                   |       |   |  |
| X = ±.2 [ .08] FRACTIONS  |                 | L ≤ 12 [305] = +1 [25] / -0                 |                   |       | SHEET 1 OF 1  |  |
| XX = ±.02 [ .51] ± 1/32   |                 | 12 [305] < L ≤ 60 [1524] = +2 [51] / -0     |                   |       |   |  |
| XXX = ±.005 [ .13] ANGLES ± 1°  |                 | 60 [1524] < L ≤ 120 [3048] = +4 [102] / -0  |                   |       |   |  |
|   |                 | 120 [3048] < L ≤ 300 [7620] = +6 [152] / -0 |                   |       |   |  |
| 300 [7620] < L ≤ +5% / -0   |                 |   |                   |       |   |  |
| ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.  |                 |   |                   |       | SCALE N/A   |  |
| SIZE A  | CAGE CODE 3EKR5 | DRAWN BY DMAY                               | ITEM NO. FMCA2418 | REV A |   |  |