



LABEL:

FAIRVIEW MICROWAVE
FMIR1032
D/C: XXXX



THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS, DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

<div><div><div></div><div></div><div></div></div><div><div></div><div></div><div></div></div></div> <div><div>an INFINITE® brand</div></div>				Fairview Microwave			
TITLE							
UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS				THIRD-ANGLE PROJECTION			
TOLERANCES:				CABLE LENGTH (L) TOLERANCES:			
X = ±.2 [5.08] FRACTIONS				L ≤ 12 [305] = +1 [25] / -0			
.XX = ±.02 [51] ± 1/32				12 [305] < L ≤ 60 [1524] = +2 [51] / -0			
.XXX = ±.005 [13] ANGLES ± 1°				60 [1524] < L ≤ 120 [3048] = +4 [102] / -0			
				120 [3048] < L ≤ 300 [7620] = +6 [152] / -0			
				300 [7620] < L = +5%L / -0			
ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.				SCALE			
SIZE				N/A			
A				REV			
CAGE CODE				A			
3FKR5							
DRAWN BY							
DFRISIELLO							
ITEM NO.							
FMIR1032							