

6

5

4





3

2


1

## REVISION

| ZONE | REV | DESCRIPTION     | DATE       | CHANGED BY | APPROVED |
|------|-----|-----------------|------------|------------|----------|
|      | A   | INITIAL RELEASE | 04/24/2023 | KGLEBOVA   | KHIETPAS |



VIEW A-A

WR-650  
CPR-650F FLANGE

## NOTES:

1. LABEL PER ILS-100-03 (FOR INTERNAL REFERENCE ONLY).  
LABEL LOCATION FOR REFERENCE ONLY.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED.  
THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED  
LEADING DIMENSIONS ARE INCHES  
DIMENSIONS IN [ ] ARE MILLIMETERS

## TOLERANCES:

.X =  $\pm .2$  [5]      FRACTIONS  
.XX =  $\pm .02$  [.5]       $\pm 1/32$   
.XXX =  $\pm .005$  [.13]      ANGLES  $\pm 1^\circ$


## CABLE LENGTH TOLERANCES:

$\leq 12$  [305] =  $\pm 1$  [25] / -0  
>12 [305]  $\leq 60$  [1524] =  $\pm 2$  [51] / -0  
>60 [1524]  $\leq 120$  [3048] =  $\pm 4$  [102] / -0  
>120 [3048]  $\leq 300$  [7620] =  $\pm 6$  [152] / -0  
>300 [7620] =  $\pm 5\%$  / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY  
AND SUBJECT TO CHANGE WITHOUT NOTICE.



Website: [www.FairviewMicrowave.com](http://www.FairviewMicrowave.com)  
Phone: 1.800.715.4396 | 1.972.649.6678



INTERPRET ALL DIMENSIONS AND  
TOLERANCES PER ASME Y14.5

SCALE  
NONE

SHEET  
1 OF 1

## DESCRIPTION

WR-650 STANDARD GAIN HORN ANTENNA, 1.13-1.73 GHz,  
10 dBi GAIN, CPR-650F FLANGE

| SIZE | CAGE CODE | DRAWN BY | ITEM NO.    | REV |
|------|-----------|----------|-------------|-----|
| A    | 3FKR5     | KGLEBOVA | FMWAN650-10 | A   |

6

5

4

3

2

1